











Optional Styli for Surftest and Formtracer SV-C series



178-396-2 : Detector 0.75 mN
178-397-2 : Detector 4 mN

Specifications

Probes **178-396-2:**
0,75 mN measuring force with the standard
stylus 12AAC731 (radius 2 μm , angle 60°)
178-397-2:
4 mN measuring force with stylus 12AAB403
(radius 5 μm , angle 90°)

Stylus		Nose pad																						
Standard		No. 12AAB345																						
	<table><tr><th>No.</th><th>Radius</th><th>Angle</th></tr><tr><td>12AAE882</td><td>1 μm</td><td>60°</td></tr><tr><td>12AAE924</td><td>1 μm</td><td>90°</td></tr><tr><td>12AAC731</td><td>2 μm</td><td>60°</td></tr><tr><td>12AAB403</td><td>5 μm</td><td>90°</td></tr><tr><td>12AAB415</td><td>10 μm</td><td>90°</td></tr><tr><td>12AAE883</td><td>250 μm</td><td>60°</td></tr></table>	No.	Radius	Angle	12AAE882	1 μm	60°	12AAE924	1 μm	90°	12AAC731	2 μm	60°	12AAB403	5 μm	90°	12AAB415	10 μm	90°	12AAE883	250 μm	60°		
No.	Radius	Angle																						
12AAE882	1 μm	60°																						
12AAE924	1 μm	90°																						
12AAC731	2 μm	60°																						
12AAB403	5 μm	90°																						
12AAB415	10 μm	90°																						
12AAE883	250 μm	60°																						
For small hole		No. 12AAB346																						
	<table><tr><th>No.</th><th>Radius</th><th>Angle</th></tr><tr><td>12AAC732</td><td>2 μm</td><td>60°</td></tr><tr><td>12AAB404</td><td>5 μm</td><td>90°</td></tr><tr><td>12AAB416</td><td>10 μm</td><td>90°</td></tr></table>	No.	Radius	Angle	12AAC732	2 μm	60°	12AAB404	5 μm	90°	12AAB416	10 μm	90°											
No.	Radius	Angle																						
12AAC732	2 μm	60°																						
12AAB404	5 μm	90°																						
12AAB416	10 μm	90°																						
For extra small hole		No. 12AAB347																						
	<table><tr><th>No.</th><th>Radius</th><th>Angle</th></tr><tr><td>12AAC733</td><td>2 μm</td><td>60°</td></tr><tr><td>12AAB405</td><td>5 μm</td><td>90°</td></tr><tr><td>12AAB417</td><td>10 μm</td><td>90°</td></tr></table>	No.	Radius	Angle	12AAC733	2 μm	60°	12AAB405	5 μm	90°	12AAB417	10 μm	90°											
No.	Radius	Angle																						
12AAC733	2 μm	60°																						
12AAB405	5 μm	90°																						
12AAB417	10 μm	90°																						
Ultra small hole																								
	<table><tr><th>No.</th><th>Radius</th><th>Angle</th></tr><tr><td>12AAJ662</td><td>250 μm</td><td>-</td></tr></table>	No.	Radius	Angle	12AAJ662	250 μm	-																	
No.	Radius	Angle																						
12AAJ662	250 μm	-																						
For extra minute hole		No. 12AAB344																						
	<table><tr><th>No.</th><th>Radius</th><th>Angle</th></tr><tr><td>12AAC734</td><td>2 μm</td><td>60°</td></tr><tr><td>12AAB406</td><td>5 μm</td><td>90°</td></tr><tr><td>12AAB418</td><td>10 μm</td><td>90°</td></tr></table>	No.	Radius	Angle	12AAC734	2 μm	60°	12AAB406	5 μm	90°	12AAB418	10 μm	90°											
No.	Radius	Angle																						
12AAC734	2 μm	60°																						
12AAB406	5 μm	90°																						
12AAB418	10 μm	90°																						