

### **GUARDIAN™2000**

**Hotplate Stirrers** 



### Rugged and Reliable Analog Hotplates and Stirrers for General **Purpose Heating and Stirring**

Dependable OHAUS Guardian 2000™ Hotplates and Stirrers are ideal for education and other lab environments that require affordable, everyday fast heating and reliable stirring up to 15L. All three sizes offer simple knob control to easily adjust the heating and stirring functions. The durable housing includes a built-in support rod holder which accepts the optional support rod. Stirring models include PTFE coated stir bars.

### **Unique Features:**

- Powerful stirring and fast heating at an economical price. Safely heat up to 500°C and stir up to 15L with easy to use knob control for simple and reliable everyday heating and stirring in the lab.
- Designed to last the rugged metal housing has a spill resistant design for long life in the lab under harsh conditions. The smooth, chemical-resistant ceramic top plate is perfect for easy clean up.
- Safety is of utmost importance the prominent hot top indicator light illuminates when the heater is above 40°C, keeping the end user safe during all heating applications.

### **GUARDIAN**™2000 Hotplate Stirrers

### **Specifications**

Model	e-G21ST04R	e-G21HP04C	e-G21HS04C			
Function	Stirring	Heating	Heating and Stirring			
Top Plate Size	4 x 4 in / 10.2 x 10.2 cm					
Speed Range	200 - 1600 rpm	-	200 - 1600 rpm			
Temperature Range	-	70 °C - 500 °C				
Control		Analog				
Capacity	15 L					
Top Plate Material	Resin	Ceramic				
Dimensions (H x L x W)		4.3 x 10.4 x 6.4 in / 11.0 x 26.4 x 16.3 cm				
Net Weight	4.7 lb. / 2.1 kg	4.0 lb. / 1.8 kg	5.5 lb. / 2.5 kg			
Power	100V-120V ~2A 50/60Hz 220V-240V ~1A 50/60Hz	100V-120V ~5A 50/60Hz 220V-240V ~4A 50/60Hz				
Power Consumption	35W (100~120V) / 35W (220~240V)	505W (100~120V) / 505W (220~240V)	535W (100~120V) / 535W (220~240V)			
Working Environment	41 °F – 104 °F, 80 % RH, non-condensing / 5 °C – 40 °C, 80 % RH, non-condensing					

Model	e-G21ST07R	e-G21HP07C	e-G21HS07C				
Function	Stirring	Heating	Heating and Stirring				
Top Plate Size	7 x 7 in / 17.8 x 17.8 cm						
Speed Range	200 - 1600 rpm	_	200 - 1600 rpm				
Temperature Range	-	70 ℃ -	500 °C				
Control		Analog					
Capacity		15 L					
Top Plate Material	Resin	Ceramic					
Dimensions (H x L x W)	4,	4.4 x 12.5 x 8.8 in / 11.2 x 31.8 x 22.3 cm					
Net Weight	6.2 lb. / 2.8 kg	7.1 lb. / 3.2 kg	8.6 lb. / 3.9 kg				
Power	100V-120V ~2A 50/60Hz 220V-240V ~1A 50/60Hz		10A 50/60Hz ~7A 50/60Hz				
Power Consumption	35W (100~120V) 35W (220~240V)	1005W (100~120V) 1005W (220~240V)	1035W (100~120V) 1035W (220~240V)				
Working Environment	41 °F – 104 °F, 80 % RH, non-condensing / 5 °C – 40 °C, 80 % RH, non-condensing						

Model	e-G21STRDS	e-G21HPRDS	e-G21HSRDS				
Function	Stirring	Heating	Heating and Stirring				
Top Plate Size		5.3 in diameter / 13.5 cm diameter					
Speed Range	200 - 1600 rpm	200 - 1600 rpm –					
Temperature Range	_	50 °C - 380 °C					
Control		Analog					
Capacity	15 L						
Top Plate Material	Ceramic Coated Stainless Steel						
Dimensions (H x L x W)	4.0 x 10.4 x 6.4 in / 10.1 x 26.4 x 16.3 cm						
Net Weight	5.1 lb. / 2.3 kg	4.0 lb. / 1.8 kg	5.5 lb. / 2.5 kg				
Power	100V-120V ~5A 50/60Hz 220V-240V ~4A 50/60Hz		~5A 50/60Hz ~4A 50/60Hz				
Power Consumption	35W (100~120V) 35W (220~240V)	505W (100~120V) 505W (220~240V)	535W (100~120V) 535W (220~240V)				
Working Environment	41 °F – 104 °F, 80 % RH	41 °F – 104 °F, 80 % RH, non-condensing / 5 °C – 40 °C, 80 % RH, non-condensing					

# **GUARDIAN™2000** Hotplate Stirrers Specifications & Accessories

GUARDIAN 2000					
Application Modes	Boiling Liquids, Basic Sample and Solution Preparation, Dissolving Buffers and Reagents, Preparing Media, Concentrating Samples				

Item No.	Description	e-G21ST04R	e-G21HP04C	e-G21HS04C	e-G21ST07R	e-G21HP07C	e-G21HS07C	e-G21STRDS	e-G21HPRDS	e-G21HSRDS
30500597	Vessel Clamp									
30500598	Stir Bar Retriever									
30400147	Spinbar 2.5 cm PTFE									
30400148	Spinbar 3.8 cm PTFE							•		
30400149	Spinbar 7 cm PTFE						•	•		
30400150	Spinbar 10 cm with Pivot Ring PTFE	•		•	•		•	•		•
30692826	Holder Kit Thermometer e-G31		•	•		•	•		•	•
30726783*	Spinbar with a Pivot 3.8 cm PTFE	•		•			•	•		•


<sup>\* 3076783</sup> is a pack of 5 spinbars




## **GUARDIAN**™2000 Hotplate Stirrers

### **Outline Dimensions**


### e-G21HS04C, e-G21HP04C, e-G21ST04R



#### e-G21HSRDS, e-G21HPRDS, e-G21STRDS



#### e-G21HS07C, e-G21HP07C, e-G21ST07R



### **Other Features and Equipment**

Green indicator lights when unit is heating and stirring with simple control knobs for easy temperature and speed adjustments, one PTFE coated stir bar (included with stirring models), ON/OFF switch for heater disconnect, built-in support rod holder

### Compliance

- Product Safety: CE, TUV, TÜV SÜD certified to CAN/CSA C22.2 61010-1; CAN/CSA C22.2 61010-2-010; CAN/CSA C22.2 61010-2-051; UL 61010-1; UL 61010-2-010; UL 61010-2-051
- Electromagnetic Compatibility: Canada ICES-003 Class A; FCC Part 15 Class A
- · Other: IP21



