



## Easy to Use:

Apply liberally to the areas to be cleaned. Wait 2-3 minutes to allow emulsifiers to penetrate. Wipe dry with a lint-free cloth such as ACL LF50 Heavy Duty Lint Free Wipes or ACL 8099 Lint Free Wipe.

### Product #6001S

24 2-oz bottles per case; finger spray

### Product #6001

12 quarts per case;includes trigger spray

### Product #6002

4 gallons per case

**Product #6002**-5 5-gallon pail

**Product #6001-2** 50 gallons per drum



# 6001, 6002 Mat & Table Top Cleaner

# Static dissipative cleaner for ESD mats

ACL Mat & Table Top Cleaner is a multi-purpose static dissipative rejuventating cleaner that is designed for maintaining the surface resistivity of ESD mats. It is the ideal cleaner for areas in which static-sensitive devices are assembled, tested, and handled, but can also be used in areas that require a mild but effective cleaner. This non-abrasive formula cleans and restores dead spots that have lost electrical characteristics. It is safe to use on the workbench, table tops and anti-static mats, including rubber and vinyl.

Mat & Table Top Cleaner is a non-flammable cleaner that leaves no film or streaks. It effectively removes flux residues, oily finger marks, grease, nicotine, dirt, grime and inorganic contaminants. It also removes dirt on chair mats and other anti-static mats without degrading the surface's anti-static properties.

### Features:

- Response Cleans, rejuvenates, and extends the life of ESD mats
- Contains no alkali or ammonia
- **®** Contains no chemical on RoHS and REACH SvHC
- **No GHS classification**
- Meets or exceeds Mil 81705 & NFPA 56A with an electrostatic decay time of .1 second according to Federal Test Method 4046

ACL**Staticide** 







