



DIGITAL LIGHT METERS KEW 5204 / 5204BT



- Wide Range Illuminance Measurement 0.0 lx to 199900 lx
- With auto-zero-adjustment function to achieve precise measurements.
- Detachable & Rotatable Light Sensor
- Data Hold Function
- MAX/MIN Function
- Large LCD with Back Light
- Bluetooth communication functions (5204BT only)






KEW 5204/5204BT Specification

•							
Light detector	Silicon photo diode						
Measuring Range	0.0 - 199900 lx						
Range	199.9/1999/19990/199900 lx						
Resolution	0.1 lx						
Accuracy	±4%rdg±5dgt (23°C±2°C)						
Angle deviation from cosine characteristics	10° ±1.5%, 30° ±3%, 60° ±10%, 80° ±30%						
Temperature characteristics	±5% (at 23°C reference and a range of 0 to 40°C)						
Relative spectral sensitivity characteristics	Deviation from spectral luminous efficiency: 9% or less						
Response time	Auto range: 5s or less Manual range: 2s or less						
Operation Temperature/	0°C - 40°C, 80%RH or less						
Humidity	(without condensation)						
Storage Temperature/	-10°C - 60°C, 70%RH or less						
Humidity	(without condensation)						
Auto power off	30 min.						
Applicable Standards	JIS C 1609-1:2006, IEC 61326						
Communication interface*	Bluetooth® Ver.5.0						
Power source	R6/LR6(AA)(1.5V) × 2						
Dimensions	169(L) × 63(W) × 37(D)mm						
Weight	210g approx.						
Accessories	9195(Carrying case), Instruction Manual LR6(AA) × 2						

^{*} KEW 5204BT only

Relative Spectral Response Characteristics in the Visible Spectrum



Adequate Light Levels for Your Working or at Your Work Areas

LUXES (lx)	3,000	2,000	1,500	1,000	750	500 3	00 20	00 1:	50 1	00 7	5	50	30	20	15
OFFICE					Director room		Inquiry office Dining room Stair Night-duty room			-	Indoor omercono		,		
	-				Electrical Recep	il room computer room tion room station	Library, 1 Dressing Toilet, lav	room	Warehou Lift, Pass		Indoor emergency staircase		y	F	
FACTORY							Stair		-						
	-	Ex	tra fine visua ork		gn room ing room	-	Control room, Electric room Air conditioning machine room, lavatory, Toilet		Entrance Passage Warehou	Path	Indoor emergency staircase		у	-	
SCH00L				Draw	Classroo Faculty r Drawing room Dining ro Gymnasi Night-du		oom, om, um	Stair							
	Electronic corr Experimenta Reading r					g classroom, computer room ental laboratory ng room care room	rputer room Haboratory room		Passage				_		

Use the application KEW Smart* to improve work effiency.

Download and install our special application "KEW Smart*" in your smartphone or tablet device for logging the measured values. Measured values can be saved in your smartphone or tablet device in csv format: the data is editable in




Please search KEW Smart*




Application for iOS
Free iOS software "KEW smart*" is available on "APP Store".
Supporting iOS 10.0 or later.

Detachable & Rotatable Light Sensor



The light sensing probe can be fixed on the meter parallel or perpendicular to the LCD Display.

Or it may be detached from the unit to fit the measuring requirement.





Please read the "Safety Warnings" in the instruction manual supplied with the instrument thoroughly and completely Safety Warnings: If the instruction maintain supplied with the supplied to operate the instrument on a correct power supply and voltage rating marked on each instrument.

For inquires or orders:



Bluetooth is a trademark or registered trademark of Bluetooth SIG. Inc. Android is a trademark or registered trademark of Google Inc. iOS is a trademark or registered trademark of Cisco Technology, Inc. in the United States and other countrie